



### Main

Range	Prisma
Product name	Prisma G
Product or component type	Side panel
IP degree of protection	IP30
Accessory / separate part category	Enclosure accessory Spare part
Range compatibility	Prisma G : enclosure
Special colour options	Yes

### Complementary

Installation description	Floor-standing enclosure
Mounting location	Side
Number of vertical modules [50 mm]	30
Quantity per set	Set of 1
Height	1525 mm
Width	200 mm
Depth	180 mm
Product weight	3.1 kg
Surface finish	Glossy Textured epoxy polyester
Colour	White RAL 9001

### Environment

IP degree of protection	IP30
IK degree of protection	IK07 without door conforming to EN/IEC 62262 IK08 with door
Protective treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder

## Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1809 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product environmental profile	Available
Product end of life instructions	Available

## Contractual warranty

Warranty period	18 months
-----------------	-----------