



Main

Range	Prisma
Product name	Prisma G
Product or component type	Side panel
IP degree of protection	IP30
Accessory / separate part category	Enclosure accessory Spare part
Range compatibility	Prisma G : enclosure
Special colour options	Yes

Complementary

Installation description	Wall-mounted enclosure
Mounting location	Side
Number of vertical modules [50 mm]	12
Quantity per set	Set of 1
Height	625 mm
Width	200 mm
Depth	180 mm
Product weight	1.29 kg
Surface finish	Glossy Textured epoxy polyester
Colour	White RAL 9001

Environment

IP degree of protection	IP30
IK degree of protection	IK07 without door conforming to EN/IEC 62262 IK08 with door
Protective treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1809 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Available

Contractual warranty

Warranty period	18 months
-----------------	-----------