



Main

| | |
|------------------------------------|-----------------------------------|
| Range | Prisma |
| Product name | Prisma G |
| Product or component type | Side panel |
| IP degree of protection | IP30 |
| Accessory / separate part category | Enclosure accessory Spare part |
| Range compatibility | Prisma G : enclosure |
| Special colour options | Yes |

Complementary

| | |
|------------------------------------|------------------------------------|
| Installation description | Wall-mounted enclosure |
| Mounting location | Side |
| Number of vertical modules [50 mm] | 15 |
| Quantity per set | Set of 1 |
| Height | 775 mm |
| Width | 200 mm |
| Depth | 180 mm |
| Product weight | 1.58 kg |
| Surface finish | Glossy Textured epoxy polyester |
| Colour | White RAL 9001 |

Environment

| | |
|-------------------------|--|
| IP degree of protection | IP30 |
| IK degree of protection | IK07 without door conforming to EN/IEC 62262 IK08 with door |
| Protective treatment | Electrophoresis treatment and hot-polymerised polyester epoxy powder |

Offer Sustainability

| | |
|----------------------------------|---|
| Sustainable offer status | Green Premium product |
| RoHS (date code: YYWW) | Compliant - since 1809 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity |
| REACH | Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold |
| Product environmental profile | Available |
| Product end of life instructions | Available |

Contractual warranty

| | |
|-----------------|-----------|
| Warranty period | 18 months |
|-----------------|-----------|