



### Main

Range	Prisma
Product name	Prisma G
Product or component type	Side panel
IP degree of protection	IP30
Accessory / separate part category	Enclosure accessory Spare part
Range compatibility	Prisma G : enclosure
Special colour options	Yes

### Complementary

Installation description	Floor-standing enclosure
Mounting location	Side
Number of vertical modules [50 mm]	36
Quantity per set	Set of 1
Height	1830 mm
Depth	180 mm
Surface finish	Glossy Textured epoxy polyester
Colour	White RAL 9001

### Environment

IP degree of protection	IP30
IK degree of protection	IK07 without door conforming to EN/IEC 62262 IK08 with door
Protective treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder

### Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1751 - Schneider Electric declaration of conformity

 Schneider Electric declaration of conformity

REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations