



Main

Range	Prisma
Range compatibility	Prisma G
Product or component type	Rail
Accessory / separate part category	Installation accessory
Type of rail	Modular Adjustable
Installed device	TeSys : fixed GV3 TeSys : fixed GV2L TeSys : fixed GV2P Compact : fixed NG160 with earth leakage protection - control: toggle Compact : fixed NG160 without earth leakage protection - control: toggle Compact : fixed NG160 NA without earth leakage protection - control: toggle Compact : fixed NSXm without earth leakage protection - control: toggle - vertical installation Compact : fixed NSXm with earth leakage protection - control: toggle - vertical installation
Poles description	9 x 3P : fixed : GV2L 9 x 3P : fixed : GV2P 1 x 3P : fixed : NG160 1 x 3P : fixed : NG160 NA 7 x 3P : fixed : GV3 1 x 4P : fixed : NG160 1 x 4P : fixed : NG160 NA 1 x 3P or 4P : fixed : NSXm vertical installation

Complementary

Installation description	Floor-standing enclosure - width 600 mm Wall-mounted enclosure - width 600 mm
Number of vertical modules [50 mm]	3 module(s) : GV2L , direct in 600 mm Wide floor-standing enclosure 3 module(s) : GV2L , direct in 600 mm Wide wall-mounted enclosure 3 module(s) : GV2P , direct in 600 mm Wide floor-standing enclosure 3 module(s) : GV2P , direct in 600 mm Wide wall-mounted enclosure 5 module(s) : GV3 , direct in 600 mm Wide floor-standing enclosure 5 module(s) : GV3 , direct in 600 mm Wide wall-mounted enclosure 5 module(s) : NG160 without earth leakage protection , direct in 600 mm Wide floor-standing enclosure 5 module(s) : NG160 without earth leakage protection , direct in 600 mm Wide wall-mounted enclosure

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

5 module(s) : NG160 NA without earth leakage protection , direct in 600 mm Wide floor-standing enclosure
 5 module(s) : NG160 NA without earth leakage protection , direct in 600 mm Wide wall-mounted enclosure
 7 module(s) : NSXm without earth leakage protection , direct in 600 mm Wide floor-standing enclosure
 7 module(s) : NSXm without earth leakage protection , direct in 600 mm Wide wall-mounted enclosure
 7 module(s) : NSXm without earth leakage protection , connection block in 600 mm Wide floor-standing enclosure
 7 module(s) : NSXm without earth leakage protection , connection block in 600 mm Wide wall-mounted enclosure
 5 module(s) : NG160 with earth leakage protection , direct in 600 mm Wide floor-standing enclosure
 5 module(s) : NG160 with earth leakage protection , direct in 600 mm Wide wall-mounted enclosure
 7 module(s) : NSXm with earth leakage protection , direct in 600 mm Wide floor-standing enclosure
 7 module(s) : NSXm with earth leakage protection , direct in 600 mm Wide wall-mounted enclosure
 7 module(s) : NSXm with earth leakage protection , connection block in 600 mm Wide floor-standing enclosure
 7 module(s) : NSXm with earth leakage protection , connection block in 600 mm Wide wall-mounted enclosure

9 mm pitches	48
Quantity per set	Set of 1
Width	600 mm
Product weight	0.34 kg
Colour	Grey
Material	Metal

Environment

Standards	IEC 61439-2 IEC 61439-1
Product certifications	ASEFA

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0807 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available Product Environmental Profile
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------