



### Main

Range	Prisma
Range compatibility	Prisma G
Product or component type	Rail
Accessory / separate part category	Installation accessory
Type of rail	Modular
Installed device	<p>Multi 9 : fixed modular device                      Acti 9 : fixed modular device                      TeSys : fixed GV2LE                      TeSys : fixed GV2ME                      TeSys : fixed GV2RTn                      Multi 9 : fixed modular device &lt;= 40 A                      Acti 9 : fixed modular device &lt;= 40 A                      Multi 9 : fixed NG125 with earth leakage protection - control: toggle                      Multi 9 : fixed NG125 without earth leakage protection - control: toggle                      Multi 9 : fixed NG125 NA - control: toggle                      Acti 9 : fixed C120 with earth leakage protection - control: toggle                      Acti 9 : fixed C120 without earth leakage protection - control: toggle                      Compact : fixed INS40 - control: direct front rotary handle - vertical installation                      Compact : fixed INS63 - control: direct front rotary handle - vertical installation                      Compact : fixed INS100 - control: direct front rotary handle - vertical installation                      Compact : fixed INS125 - control: direct front rotary handle - vertical installation                      Compact : fixed INS160 - control: direct front rotary handle - vertical installation                      Acti 9 : fixed iC120 with earth leakage protection - control: toggle                      Acti 9 : fixed iC120 without earth leakage protection - control: toggle</p>
Poles description	<p>1 x 3P : fixed : NG125                      1 x 3P : fixed : NG125 NA                      1 x 3P : fixed : C120                      1 x 4P : fixed : NG125                      1 x 4P : fixed : NG125 NA                      1 x 4P : fixed : C120                      1 x 3P : fixed : INS40 vertical installation                      1 x 3P : fixed : INS63 vertical installation                      1 x 3P : fixed : INS100 vertical installation                      1 x 3P : fixed : INS125 vertical installation                      1 x 3P : fixed : INS160 vertical installation                      1 x 3P : fixed : iC120                      1 x 4P : fixed : INS40 vertical installation                      1 x 4P : fixed : INS63 vertical installation                      1 x 4P : fixed : INS100 vertical installation</p>

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

1 x 4P : fixed : INS125 vertical installation  
 1 x 4P : fixed : INS160 vertical installation  
 1 x 4P : fixed : iC120  
 4 x 3P : fixed : GV2LE  
 4 x 3P : fixed : GV2ME  
 4 x 3P : fixed : GV2RTn

## Complementary

Installation description	Floor-standing duct - width 300 mm Wall-mounted duct - width 300 mm
Number of vertical modules [50 mm]	4 module(s) : C120 without earth leakage protection , direct in 300 mm Wide floor-standing duct 4 module(s) : C120 without earth leakage protection , direct in 300 mm Wide wall-mounted duct 3 module(s) : GV2LE , direct in 300 mm Wide floor-standing duct 3 module(s) : GV2LE , direct in 300 mm Wide wall-mounted duct 3 module(s) : GV2ME , direct in 300 mm Wide floor-standing duct 3 module(s) : GV2ME , direct in 300 mm Wide wall-mounted duct 3 module(s) : GV2RTn , direct in 300 mm Wide floor-standing duct 3 module(s) : GV2RTn , direct in 300 mm Wide wall-mounted duct 4 module(s) : iC120 without earth leakage protection , direct in 300 mm Wide floor-standing duct 4 module(s) : iC120 without earth leakage protection , direct in 300 mm Wide wall-mounted duct 4 module(s) : INS100 , direct in 300 mm Wide floor-standing duct 4 module(s) : INS100 , direct in 300 mm Wide wall-mounted duct 5 module(s) : INS100 , direct in 300 mm Wide floor-standing duct 5 module(s) : INS100 , direct in 300 mm Wide wall-mounted duct 4 module(s) : INS125 , direct in 300 mm Wide floor-standing duct 4 module(s) : INS125 , direct in 300 mm Wide wall-mounted duct 5 module(s) : INS125 , direct in 300 mm Wide floor-standing duct 5 module(s) : INS125 , direct in 300 mm Wide wall-mounted duct 4 module(s) : INS160 , direct in 300 mm Wide floor-standing duct 4 module(s) : INS160 , direct in 300 mm Wide wall-mounted duct 5 module(s) : INS160 , direct in 300 mm Wide floor-standing duct 5 module(s) : INS160 , direct in 300 mm Wide wall-mounted duct 4 module(s) : INS40 , direct in 300 mm Wide floor-standing duct 4 module(s) : INS40 , direct in 300 mm Wide wall-mounted duct 4 module(s) : INS63 , direct in 300 mm Wide floor-standing duct 4 module(s) : INS63 , direct in 300 mm Wide wall-mounted duct 3 module(s) : modular device <= 40 A , direct in 300 mm Wide floor-standing duct 3 module(s) : modular device <= 40 A , direct in 300 mm Wide wall-mounted duct 4 module(s) : modular device , direct in 300 mm Wide floor-standing duct 4 module(s) : modular device , direct in 300 mm Wide wall-mounted duct 4 module(s) : NG125 without earth leakage protection , direct in 300 mm Wide floor-standing duct 4 module(s) : NG125 without earth leakage protection , direct in 300 mm Wide wall-mounted duct 4 module(s) : NG125 NA , direct in 300 mm Wide floor-standing duct 4 module(s) : NG125 NA , direct in 300 mm Wide wall-mounted duct 4 module(s) : C120 with earth leakage protection , direct in 300 mm Wide floor-standing duct 4 module(s) : C120 with earth leakage protection , direct in 300 mm Wide wall-mounted duct 4 module(s) : iC120 with earth leakage protection , direct in 300 mm Wide floor-standing duct 4 module(s) : iC120 with earth leakage protection , direct in 300 mm Wide wall-mounted duct 4 module(s) : NG125 with earth leakage protection , direct in 300 mm Wide floor-standing duct 4 module(s) : NG125 with earth leakage protection , direct in 300 mm Wide wall-mounted duct
9 mm pitches	20
Quantity per set	Set of 1
Height	93.5 mm
Width	300 mm
Depth	50 mm
Product weight	0.14 kg
Colour	Grey
Material	Metal

## Environment

Standards	IEC 61439-1 IEC 61439-2
Product certifications	ASEFA

## Offer Sustainability

Sustainable offer status	Green Premium product
--------------------------	-----------------------

RoHS (date code: YYWW)	Compliant - since 0807 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product environmental profile	Available <a href="#">Product Environmental Profile</a>
Product end of life instructions	Need no specific recycling operations

### Contractual warranty

Warranty period	18 months
-----------------	-----------