



Main

Range	Prisma
Range compatibility	Prisma G
Product or component type	Mounting plate
Accessory / separate part category	Installation accessory
Mounting plate description	Dedicated
Installed device	Compact : fixed NSXm without earth leakage protection - control: toggle - horizontal installation Compact : fixed NSXm with earth leakage protection - control: toggle - horizontal installation
Poles description	1 x 3P or 4P : fixed : NSXm horizontal installation

Complementary

Installation description	Floor-standing enclosure - width 600 mm Wall-mounted enclosure - width 600 mm Floor-standing enclosure - width 850 mm Floor-standing enclosure + duct - width 600 + 300 mm Wall-mounted enclosure + duct - width 600 + 300 mm
Number of vertical modules [50 mm]	3 module(s) : NSXm without earth leakage protection , direct in 600 mm Wide floor-standing enclosure 3 module(s) : NSXm without earth leakage protection , direct in 600 mm Wide wall-mounted enclosure 3 module(s) : NSXm without earth leakage protection , direct in 600 + 300 mm Wide floor-standing enclosure + duct 3 module(s) : NSXm without earth leakage protection , direct in 600 + 300 mm Wide wall-mounted enclosure + duct 3 module(s) : NSXm without earth leakage protection , direct in 850 mm Wide floor-standing enclosure 3 module(s) : NSXm with earth leakage protection , direct in 600 mm Wide floor-standing enclosure 3 module(s) : NSXm with earth leakage protection , direct in 600 mm Wide wall-mounted enclosure 3 module(s) : NSXm with earth leakage protection , direct in 600 + 300 mm Wide floor-standing enclosure + duct 3 module(s) : NSXm with earth leakage protection , direct in 600 + 300 mm Wide wall-mounted enclosure + duct 3 module(s) : NSXm with earth leakage protection , direct in 850 mm Wide floor-standing enclosure
Surface finish	Matt Smooth
Protective treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Colour	White RAL 9001

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Environment

Standards	IEC 61439-2
Product certifications	ASEFA
