



Main

Range	Prisma
Range compatibility	Prisma G
Product or component type	Mounting plate
Accessory / separate part category	Installation accessory
Installed device	Fupact : fixed ISFT160 - control: fuse carriers handle - vertical installation Fupact : fixed ISFT100N - control: fuse carriers handle - vertical installation
Poles description	4 x 3P : fixed : ISFT160 vertical installation 6 x 3P : fixed : ISFT100N vertical installation

Complementary

Installation description	Floor-standing enclosure - width 600 mm Wall-mounted enclosure - width 600 mm
Number of vertical modules [50 mm]	8 module(s) : ISFT100N, rear connection on busbar in 600 mm Wide floor-standing enclosure 8 module(s) : ISFT100N, rear connection on busbar in 600 mm Wide wall-mounted enclosure 8 module(s) : ISFT160, rear connection on busbar in 600 mm Wide floor-standing enclosure 8 module(s) : ISFT160, rear connection on busbar in 600 mm Wide wall-mounted enclosure
Height	250 mm
Product weight	4.26 kg
Colour	White RAL 9001

Environment

Standards	IEC 61439-2
Product certifications	ASEFA

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0815 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold

Reference not containing SVHC above the threshold

Product environmental profile	Available Product Environmental Profile
-------------------------------	--

Product end of life instructions	Need no specific recycling operations
----------------------------------	---------------------------------------

Contractual warranty

Warranty period	18 months
-----------------	-----------
