



### Main

Range	Prisma
Range compatibility	Prisma G Prisma Pack 250
Product or component type	Mounting plate
Accessory / separate part category	Installation accessory
Installed device	Fupact : fixed ISFT250 - control: fuse carriers handle - vertical installation
Poles description	1 x 3P : fixed : ISFT250 vertical installation

### Complementary

Installation description	Floor-standing duct - width 300 mm Wall-mounted duct - width 300 mm Pack enclosure - width 300 mm
Number of vertical modules [50 mm]	9 module(s) : ISFT250, direct in 300 mm Wide floor-standing duct 9 module(s) : ISFT250, direct in 300 mm Wide wall-mounted duct 9 module(s) : ISFT250, direct in 300 mm Wide Pack enclosure
Height	200 mm
Product weight	1.02 kg
Surface finish	Matt Smooth
Protective treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Colour	White RAL 9001

### Environment

Standards	IEC 61439-2
Product certifications	ASEFA

### Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0807 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>

REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product environmental profile	Available <a href="#">Product Environmental Profile</a>
Product end of life instructions	Need no specific recycling operations

**Contractual warranty**

Warranty period	18 months
-----------------	-----------