



Product data sheet

Specifications



MOUNTING PLATE V ISFT 100N VERTICAL W600

03126

 **Discontinued on:** Jan 8, 2021

 **Discontinued**

Main

Range	Prisma
Range Of Product	Prisma G
Product Or Component Type	Mounting plate
Accessory / Separate Part Category	Installation accessory
Range Compatibility	Prisma Prisma G enclosure
Installation Description	Floor-standing enclosure - width 600 mm Wall-mounted enclosure - width 600 mm
Installed Device	FuPact: fixed ISFT100N - control: fuse carriers handle - vertical installation
Poles Description	8 x 3P: fixed ISFT100N vertical installation
Number Of Vertical Modules [50 Mm]	8 module(s): ISFT100N, direct in 600 mm Widefloor-standing enclosure 8 module(s): ISFT100N, direct in 600 mm Widewall-mounted enclosure
Standards	IEC 61439-2
Product Certifications	ASEFA

Complementary

Protective Treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Surface Finish	Smooth Matt
Colour	White (RAL 9001)
Width	600 mm
Height	100 mm
Depth	94 mm
Net Weight	1.15 kg
Functional Unit	600 mm Prisma G floor-standing enclosure FuPact ISFT100N fixed fuse carriers handle vertical 3P 8 direct 8 175 mm 600 mm Prisma G wall-mounted enclosure FuPact ISFT100N fixed fuse carriers handle vertical 3P 8 direct 8 175 mm

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	10 cm
Package 1 Width	10.2 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Length	47 cm
Package 1 Weight	1.15 kg

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

✓ Halogen Free Plastic Parts Product

Certifications & Standards

Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
-------------------	---

China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
-----------------------	---

Environmental Disclosure	Product Environmental Profile
--------------------------	---

Circularity Profile	End of Life Information
---------------------	---