



Main

Range	Prisma
Range compatibility	Prisma G
Product or component type	Mounting plate
Accessory / separate part category	Installation accessory
Installed device	Power meters : kilowatt-hour meters - vertical installation
Poles description	1 x 4P : kilowatt-hour meters vertical installation

Complementary

Installation description	Floor-standing duct - width 300 mm Wall-mounted duct - width 300 mm
Number of vertical modules [50 mm]	9 module(s) : kilowatt-hour meters in 300 mm Wide floor-standing duct 9 module(s) : kilowatt-hour meters in 300 mm Wide wall-mounted duct
Height	400 mm
Product weight	1.06 kg
Surface finish	Matt Smooth
Protective treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Colour	White RAL 9001

Environment

Standards	IEC 61439-2
Product certifications	ASEFA

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 0807 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
Product environmental profile	Available Product Environmental Profile
Product end of life instructions	Need no specific recycling operations

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Contractual warranty

Warranty period	18 months
-----------------	-----------
