



### Main

Range	Prisma
Range compatibility	Pack 160 Prisma G Prisma Pack 250 Prisma P
Product or component type	Front plate
Accessory / separate part category	Installation accessory
Type of front plate	Cut-out Modular
Installed device	TeSys: fixed GV2L TeSys: fixed GV2LE TeSys: fixed GV2ME TeSys: fixed GV2P TeSys: fixed GV2RTn Vigilohm: IM20 Vigilohm: IM20H Vigilohm: fixed IM9 Vigilohm: IM9 Vigilohm: fixed IM9-OL Vigilohm: IM9-OL Acti 9: measurement device Multi 9: measurement device Acti 9: fixed modular device <= 40 A Multi 9: fixed modular device <= 40 A Vigirex: RH10 Vigirex: RH197M Vigirex: RH21 Vigirex: RH99
Poles description	9 x 3P: modular rail support: GV2L 9 x 3P: modular rail support: GV2LE 9 x 3P: modular rail support: GV2ME 9 x 3P: modular rail support: GV2P 9 x 3P: modular rail support: GV2RTn

### Complementary

Enclosure/Cubicle description	Floor-standing enclosure - width 600 mm Wall-mounted enclosure - width 600 mm
-------------------------------	--

Cubicle - width 650 mm depth 400 mm  
 Pack enclosure - width 555 mm  
 Pack enclosure - width 600 mm

9 mm pitches	48
Number of 18 mm modules per row	24
Number of vertical modules [50 mm]	3
Standards	IEC 61439-1 IEC 61439-2
Product certifications	ASEFA
Quantity per set	Set of 1
Height	150 mm
Width	500 mm
Net weight	0.54 kg
Material	Steel
Surface finish	Matt Smooth
Protective treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Colour	White (RAL 9001)

## Environment

IK degree of protection	IK07 conforming to EN/IEC 62262
-------------------------	---------------------------------

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Not applicable, out of EU RoHS legal scope
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations

## Contractual warranty

Warranty	18 months
----------	-----------