



Main

Range	Prisma
Range compatibility	Prisma G Prisma P
Product or component type	Front plate
Accessory / separate part category	Installation accessory
Type of front plate	Cut-out Modular
Installed device	Acti 9: fixed modular device ≤ 40 A Multi 9: fixed modular device ≤ 40 A

Complementary

Enclosure/Cubicle description	Floor-standing enclosure - width 600 mm Wall-mounted enclosure - width 600 mm Cubicle - width 650 mm depth 400 mm
Connection position	Direct connection
Number of horizontal rows	3
9 mm pitches	48
Number of 18 mm modules per row	24
Number of vertical modules [50 mm]	8
Standards	IEC 61439-2 IEC 61439-1
Product certifications	ASEFA
Quantity per set	Set of 1
Height	400 mm
Width	500 mm
Net weight	1.24 kg
Material	Steel
Surface finish	Smooth Matt

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Protective treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Colour	White (RAL 9001)

Environment

IK degree of protection	IK07 conforming to EN/IEC 62262
-------------------------	---------------------------------

Offer Sustainability

Sustainable offer status	Green Premium product
RECh Regulation	RECh Declaration
RECh free of SVHC	Yes
EU RoHS Directive	Not applicable, out of EU RoHS legal scope
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations

Contractual warranty

Warranty	18 months
----------	-----------