



Main

Range	Prisma
Range compatibility	Prisma P
Product or component type	Front plate
Accessory / separate part category	Installation accessory
Type of front plate	Cut-out
Installed device	Compact : fixed NSXm without earth leakage protection - control: toggle - vertical installation Compact : fixed NSXm without earth leakage protection - control: direct rotary handle - vertical installation Compact : fixed NSXm with earth leakage protection - control: toggle - vertical installation
Poles description	1 x 3P or 4P : mounting plate support : NSXm vertical installation
Operating position	Vertical

Complementary

Enclosure/Cubicle description	Cubicle - width 400 mm, depth 400 mm
Connection position	Direct connection
Number of vertical modules [50 mm]	5
Standards	IEC 61496-1 IEC 61439-2
Product certifications	ASEFA
Quantity per set	Set of 1
Height	250 mm
Surface finish	Matt Smooth
Protective treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Colour	White RAL 9001

Environment

IK degree of protection	IK07 conforming to EN/IEC 62262
-------------------------	---------------------------------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications.