



Main

Range	Prisma
Range compatibility	Prisma P Prisma G
Product or component type	Front plate
Accessory / separate part category	Installation accessory
Type of front plate	Cut-out
Installed device	Compact : fixed INS250 source changeover - control: direct front rotary handle - vertical installation
Poles description	1 x 3P : mounting plate support : INS250 source changeover vertical installation 2 x 3P : mounting plate support : INS250 source changeover vertical installation 1 x 4P : mounting plate support : INS250 source changeover vertical installation 2 x 4P : mounting plate support : INS250 source changeover vertical installation
Operating position	Vertical

Complementary

Enclosure/Cubicle description	Floor-standing enclosure - width 600 mm Wall-mounted enclosure - width 600 mm Cubicle - width 650 mm, depth 400 mm
Connection position	Front connection Direct connection
Number of vertical modules [50 mm]	5
Standards	IEC 61439-1 IEC 61439-2
Product certifications	ASEFA
Quantity per set	Set of 1
Height	250 mm
Width	500 mm
Product weight	0.9 kg
Material	Steel
Surface finish	Smooth Matt
Protective treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder

Colour	White RAL 9001
--------	----------------

Environment

IK degree of protection	IK07 conforming to EN/IEC 62262
-------------------------	---------------------------------

Offer Sustainability

Sustainable offer status	Green Premium product
--------------------------	-----------------------

RoHS (date code: YYWW)	Compliant Schneider Electric declaration of conformity
------------------------	---

REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
-------	--

Product environmental profile	Available Product Environmental Profile
-------------------------------	--

Product end of life instructions	Need no specific recycling operations
----------------------------------	---------------------------------------

Contractual warranty

Warranty period	18 months
-----------------	-----------
