



### Main

Range	Prisma
Range compatibility	Prisma G
IP degree of protection	IP30
Product or component type	Front plate
Accessory / separate part category	Installation accessory
Type of front plate	Cut-out
Installed device	Easypact : fixed CVS100...160 with earth leakage protection - control: toggle - vertical installation Easypact : fixed CVS250 with earth leakage protection - control: toggle - vertical installation
Poles description	1 x 4P : mounting plate support : CVS100...160 vertical installation 1 x 3P : mounting plate support : CVS100...160 vertical installation 1 x 4P : mounting plate support : CVS250 vertical installation 1 x 3P : mounting plate support : CVS250 vertical installation
Operating position	Vertical

### Complementary

Enclosure/Cubicle description	Floor-standing duct - width 300 mm Wall-mounted duct - width 300 mm
Connection position	Front connection
Type of front plate	Cut-out
Number of vertical modules [50 mm]	11
Standards	IEC 61439-2 IEC 61439-1
Product certifications	ASEFA
Quantity per set	Set of 1
Height	550 mm
Width	300 mm
Product weight	1.18 kg
Surface finish	Matt Smooth

Protective treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Colour	White RAL 9001

## Environment

IK degree of protection	IK07 conforming to EN/IEC 62262
-------------------------	---------------------------------

## Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0701 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product environmental profile	Available <a href="#">Product Environmental Profile</a>
Product end of life instructions	Need no specific recycling operations

## Contractual warranty

Warranty period	18 months
-----------------	-----------