



### Main

Range	Prisma
Range compatibility	Prisma G
IP degree of protection	IP30
Product or component type	Front plate
Accessory / separate part category	Installation accessory
Type of front plate	Cut-out
Installed device	Easypact : fixed CVS100...160 with earth leakage protection - control: toggle - horizontal installation Easypact : fixed CVS250 with earth leakage protection - control: toggle - horizontal installation
Poles description	1 x 4P : mounting plate support : CVS100...160 horizontal installation 1 x 3P : mounting plate support : CVS100...160 horizontal installation 1 x 4P : mounting plate support : CVS250 horizontal installation 1 x 3P : mounting plate support : CVS250 horizontal installation
Operating position	Horizontal

### Complementary

Enclosure/Cubicle description	Floor-standing enclosure - width 850 mm
Connection position	Direct connection
Number of vertical modules [50 mm]	4
Standards	IEC 61439-2 IEC 61439-1
Product certifications	ASEFA
Enclosure material	Front panel : painted sheet steel
Quantity per set	Set of 1
Height	200 mm
Width	750 mm
Product weight	1.44 kg
Surface finish	Matt Smooth
Protective treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Colour	White RAL 9001

### Environment

IK degree of protection	IK07 conforming to EN/IEC 62262
-------------------------	---------------------------------

Contractual warranty

---

Warranty period	18 months
-----------------	-----------

---