


# Product data sheet

Specifications



## FRONT PLATE VIGI CVS 250 HORIZONTAL FIXED TOGGLE W850 4M

03257

 **Discontinued on:** Jan 8, 2021

 **Discontinued**

### Main

Range	Prisma
Range Of Product	Prisma G
Product Or Component Type	Front plate
Accessory / Separate Part Category	Installation accessory
Range Compatibility	Prisma Prisma G enclosure
Type Of Front Plate	Cut-out
Installed Device	EasyPact: fixed CVS100...160 with earth leakage protection - control: toggle - horizontal installation EasyPact: fixed CVS250 with earth leakage protection - control: toggle - horizontal installation
Poles Description	1 x 3P: mounting plate support: CVS100...160 horizontal installation 1 x 4P: mounting plate support: CVS100...160 horizontal installation 1 x 3P: mounting plate support: CVS250 horizontal installation 1 x 4P: mounting plate support: CVS250 horizontal installation
Operating Position	Horizontal

### Complementary

Enclosure/Cubicle Description	Floor-standing enclosure - width 850 mm
Connection Position	Direct connection
Number Of Vertical Modules [50 Mm]	4
Standards	IEC 61439-2 IEC 61439-1
Product Certifications	ASEFA
Surface Finish	Matt Smooth
Protective Treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Colour	White (RAL 9001)
Height	200 mm
Width	750 mm
Net Weight	1.44 kg
Quantity Per Set	Set of 1

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Functional Unit	850 mm Prisma G floor-standing enclosure EasyPact CVS100...160 with fixed toggle horizontal 3P 1 direct with long terminal shield 4 850 mm Prisma G floor-standing enclosure EasyPact CVS100...160 with fixed toggle horizontal 4P 1 direct with long terminal shield 4 850 mm Prisma G floor-standing enclosure EasyPact CVS250 with fixed toggle horizontal 3P 1 direct with long terminal shield 4 850 mm Prisma G floor-standing enclosure EasyPact CVS250 with fixed toggle horizontal 4P 1 direct with long terminal shield 4
-----------------	--

## Environment

Ip Degree Of Protection	IP30
-------------------------	------

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3 cm
Package 1 Width	20 cm
Package 1 Length	75 cm
Package 1 Weight	1.44 kg

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information   [Yes](#)

✓ Halogen Free Plastic Parts Product

## Certifications & Standards

Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
-------------------	---

China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
-----------------------	---

Environmental Disclosure	<a href="#">Product Environmental Profile</a>
--------------------------	---