



Main

Range	Prisma
Range compatibility	Prisma Pack 250
IP degree of protection	IP30
Product or component type	Incoming functional unit
Accessory / separate part category	Installation accessory
Type of front plate	Cut-out
Installed device	Acti 9 : fixed modular device Multi 9 : fixed NG125 with earth leakage protection - control: toggle Multi 9 : fixed NG125 without earth leakage protection - control: toggle Acti 9 : fixed C120 with earth leakage protection - control: toggle Acti 9 : fixed C120 without earth leakage protection - control: toggle Compact : fixed INS40 - control: direct front rotary handle - vertical installation Compact : fixed INS63 - control: direct front rotary handle - vertical installation Compact : fixed INS100 - control: direct front rotary handle - vertical installation Compact : fixed INS125 - control: direct front rotary handle - vertical installation Compact : fixed INS160 - control: direct front rotary handle - vertical installation Acti 9 : fixed iC120 with earth leakage protection - control: toggle Acti 9 : fixed iC120 without earth leakage protection - control: toggle
Poles description	1 x 3P : modular rail support : INS100 vertical installation 1 x 4P : modular rail support : INS100 vertical installation 1 x 3P : modular rail support : INS125 vertical installation 1 x 4P : modular rail support : INS125 vertical installation 1 x 3P : modular rail support : INS160 vertical installation 1 x 4P : modular rail support : INS160 vertical installation 1 x 3P : modular rail support : INS40 vertical installation 1 x 4P : modular rail support : INS40 vertical installation 1 x 3P : modular rail support : INS63 vertical installation 1 x 4P : modular rail support : INS63 vertical installation 1 x 3P : modular rail support : C120 1 x 4P : modular rail support : C120 1 x 3P : modular rail support : iC120 1 x 4P : modular rail support : iC120 1 x 3P : modular rail support : NG125 1 x 4P : modular rail support : NG125
Operating position	Vertical

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Complementary

Enclosure/Cubicle description	Pack enclosure - width 600 mm
Number of horizontal rows	1
Number of vertical modules [50 mm]	6
Standards	IEC 61439-2 IEC 61439-1
Product certifications	ASEFA
Enclosure material	Painted sheet steel
Quantity per set	Set of 1
Height	300 mm
Width	600 mm
Product weight	1.58 kg
Surface finish	Matt Smooth
Protective treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Colour	White RAL 9001

Environment

IK degree of protection	IK07 conforming to EN/IEC 62262
-------------------------	---------------------------------

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available Product Environmental Profile
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------