



Main

Range	Prisma
Range compatibility	Prisma Pack 250
IP degree of protection	IP30
Product or component type	Incoming functional unit
Accessory / separate part category	Installation accessory
Type of front plate	Cut-out
Installed device	Multi 9 : fixed modular device Acti 9 : fixed modular device Compact : fixed NG160 with earth leakage protection - control: toggle Compact : fixed NG160 without earth leakage protection - control: toggle
Poles description	1 x 3P : modular rail support : NG160 1 x 4P : modular rail support : NG160
Operating position	Vertical

Complementary

Enclosure/Cubicle description	Pack enclosure - width 600 mm
Number of horizontal rows	1
Number of vertical modules [50 mm]	6
Standards	IEC 61439-2 IEC 61439-1
Product certifications	ASEFA
Enclosure material	Painted sheet steel
Quantity per set	Set of 1
Height	300 mm
Width	600 mm
Product weight	1.84 kg
Surface finish	Matt Smooth
Protective treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Colour	White RAL 9001

Environment

IK degree of protection	IK07 conforming to EN/IEC 62262
-------------------------	---------------------------------

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0811 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available Product Environmental Profile
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------