



Main

Range	Prisma
Range compatibility	Prisma G
IP degree of protection	IP30
Product or component type	Front plate
Accessory / separate part category	Installation accessory
Type of front plate	Cut-out
Installed device	Easypact : fixed CVS400 without earth leakage protection - control: toggle - vertical installation Easypact : fixed CVS630 without earth leakage protection - control: toggle - vertical installation
Poles description	1 x 3P : mounting plate support : CVS400 vertical installation 1 x 4P : mounting plate support : CVS400 vertical installation 1 x 3P : mounting plate support : CVS630 vertical installation 1 x 4P : mounting plate support : CVS630 vertical installation
Operating position	Vertical

Complementary

Enclosure/Cubicle description	Floor-standing duct - width 300 mm Wall-mounted duct - width 300 mm
Connection position	Direct connection
Type of front plate	Cut-out
Number of vertical modules [50 mm]	8
Standards	IEC 61439-2 IEC 61439-1
Product certifications	ASEFA
Quantity per set	Set of 1
Height	400 mm
Width	300 mm
Product weight	0.86 kg
Material	Steel
Surface finish	Matt Smooth

Protective treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Colour	White RAL 9001

Environment

IK degree of protection	IK07 conforming to EN/IEC 62262
-------------------------	---------------------------------

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0701 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available Product environmental
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------