



Main

| | |
|------------------------------------|--|
| Range | Prisma |
| Range compatibility | Prisma P Prisma G Prisma Pack 250 |
| Product or component type | Front plate |
| Accessory / separate part category | Installation accessory |
| Type of front plate | Cut-out |
| Installed device | Compact : fixed NSX100...160 with earth leakage protection - control: toggle - vertical installation Compact : fixed NSX250 with earth leakage protection - control: toggle - vertical installation Compact : plug-in NSX100...160 with earth leakage protection - control: toggle - vertical installation Compact : plug-in NSX250 with earth leakage protection - control: toggle - vertical installation |
| Poles description | 1 x 4P : mounting plate support : NSX100...160 vertical installation 1 x 3P : mounting plate support : NSX100...160 vertical installation 1 x 3P : mounting plate support : NSX250 vertical installation 1 x 4P : mounting plate support : NSX250 vertical installation |
| Operating position | Vertical |

Complementary

| | |
|------------------------------------|---|
| Enclosure/Cubicle description | Floor-standing duct - width 300 mm Wall-mounted duct - width 300 mm Cubicle - width 400 mm, depth 400 mm Pack enclosure - width 300 mm |
| Connection position | Front connection Direct connection |
| Number of vertical modules [50 mm] | 11 |
| Standards | IEC 61439-2 IEC 61439-1 |
| Product certifications | ASEFA |
| Quantity per set | Set of 1 |
| Height | 450 mm |
| Width | 300 mm |
| Product weight | 1.16 kg |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

| | |
|----------------------|--|
| Material | Steel |
| Surface finish | Smooth Matt |
| Protective treatment | Electrophoresis treatment and hot-polymerised polyester epoxy powder |
| Colour | White RAL 9001 |

Environment

| | |
|-------------------------|---------------------------------|
| IK degree of protection | IK07 conforming to EN/IEC 62262 |
|-------------------------|---------------------------------|

Offer Sustainability

| | |
|----------------------------------|---|
| Sustainable offer status | Green Premium product |
| RoHS (date code: YYWW) | Compliant - since 0750 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity |
| REACH | Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold |
| Product environmental profile | Available Product Environmental Profile |
| Product end of life instructions | Need no specific recycling operations |

Contractual warranty

| | |
|-----------------|-----------|
| Warranty period | 18 months |
|-----------------|-----------|