

Product data sheet

Specifications



FRONT PLATE NSX/CVS 250 HORIZONTAL FIXED ROTARY HANDLE W850 4M

03301

 **Discontinued on:** Apr 25, 2023

 **Discontinued**

Main

Range	Prisma
Range Of Product	Prisma G
Product Or Component Type	Front plate
Accessory / Separate Part Category	Installation accessory
Range Compatibility	Prisma Prisma G enclosure
Type Of Front Plate	Cut-out
Installed Device	EasyPact: fixed CVS100...160 without earth leakage protection - control: direct front rotary handle - horizontal installation EasyPact: fixed CVS250 without earth leakage protection - control: direct front rotary handle - horizontal installation ComPact: fixed NSX100...160 without earth leakage protection - control: direct front rotary handle - horizontal installation ComPact: fixed NSX250 without earth leakage protection - control: direct front rotary handle - horizontal installation ComPact: fixed NSX100...160 integrated earth leakage protection - control: direct front rotary handle - horizontal installation ComPact: fixed NSX250 integrated earth leakage protection - control: direct front rotary handle - horizontal installation Human-switchboard interface: 96 x 96 mm device Human-switchboard interface: HSI Enerlin'X: fixed FDM121 - control: remote control - vertical installation
Poles Description	1 x 3P: mounting plate support: CVS100...160 horizontal installation 1 x 4P: mounting plate support: CVS100...160 horizontal installation 1 x 3P: mounting plate support: CVS250 horizontal installation 1 x 4P: mounting plate support: CVS250 horizontal installation 1 x 3P: mounting plate support: NSX100...160 horizontal installation 1 x 4P: mounting plate support: NSX100...160 horizontal installation 1 x 3P: mounting plate support: NSX250 horizontal installation 1 x 4P: mounting plate support: NSX250 horizontal installation
Operating Position	Horizontal

Complementary

Enclosure/Cubicle Description	Floor-standing enclosure - width 850 mm
Connection Position	Direct connection
Number Of Vertical Modules [50 Mm]	4
Standards	IEC 61439-2 IEC 61439-1
Product Certifications	ASEFA
Surface Finish	Smooth Matt
Protective Treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Colour	White (RAL 9001)
Height	200 mm
Width	750 mm
Quantity Per Set	Set of 1
Functional Unit	850 mm Prisma G floor-standing enclosure human-switchboard interface 96 x 96 mm device 1 4 850 mm Prisma G floor-standing enclosure human-switchboard interface HSI 1 4 850 mm Prisma G floor-standing enclosure Enerlin'X FDM121 fixed remote control vertical 1 4 850 mm Prisma G floor-standing enclosure EasyPact CVS100...160 without fixed direct front rotary handle horizontal 3P 1 direct with long terminal shield 4 850 mm Prisma G floor-standing enclosure EasyPact CVS100...160 without fixed direct front rotary handle horizontal 4P 1 direct with long terminal shield 4 850 mm Prisma G floor-standing enclosure EasyPact CVS250 without fixed direct front rotary handle horizontal 3P 1 direct with long terminal shield 4 850 mm Prisma G floor-standing enclosure EasyPact CVS250 without fixed direct front rotary handle horizontal 4P 1 direct with long terminal shield 4 850 mm Prisma G floor-standing enclosure ComPact NSX100...160 without fixed direct front rotary handle horizontal 3P 1 direct with long terminal shield 4 850 mm Prisma G floor-standing enclosure ComPact NSX100...160 without fixed direct front rotary handle horizontal 4P 1 direct with long terminal shield 4 850 mm Prisma G floor-standing enclosure ComPact NSX250 without fixed direct front rotary handle horizontal 3P 1 direct with long terminal shield 4 850 mm Prisma G floor-standing enclosure ComPact NSX250 without fixed direct front rotary handle horizontal 4P 1 direct with long terminal shield 4 850 mm Prisma G floor-standing enclosure ComPact NSX100...160 integrated fixed direct front rotary handle horizontal 3P 1 direct with long terminal shield 4 850 mm Prisma G floor-standing enclosure ComPact NSX100...160 integrated fixed direct front rotary handle horizontal 4P 1 direct with long terminal shield 4 850 mm Prisma G floor-standing enclosure ComPact NSX250 integrated fixed direct front rotary handle horizontal 3P 1 direct with long terminal shield 4 850 mm Prisma G floor-standing enclosure ComPact NSX250 integrated fixed direct front rotary handle horizontal 4P 1 direct with long terminal shield 4

Environment

Ip Degree Of Protection	IP30
-------------------------	------

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.5 cm
Package 1 Width	19.9 cm
Package 1 Length	74.9 cm
Package 1 Weight	1.43 kg
Unit Type Of Package 2	P12
Number Of Units In Package 2	20
Package 2 Height	32 cm
Package 2 Width	80 cm
Package 2 Length	120 cm
Package 2 Weight	40.6 kg
Package 3 Height	32 cm

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

✓ Halogen Free Plastic Parts Product

Certifications & Standards

Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
--------------------------	---

China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
------------------------------	---

Environmental Disclosure	Product Environmental Profile
---------------------------------	---

Circularity Profile	End of Life Information
----------------------------	---