



### Main

Range	Prisma
Range compatibility	Prisma P
Product or component type	Front plate
Accessory / separate part category	Installation accessory
Type of front plate	Cut-out
Installed device	Fupact: fixed ISFT630 - control: fuse carriers handle - horizontal installation
Poles description	1 x 3P: mounting plate support: ISFT630 horizontal installation
Operating position	Horizontal

### Complementary

Enclosure/Cubicle description	Cubicle - width 650 mm depth 400 mm
Connection position	Direct connection
Number of vertical modules [50 mm]	8
Standards	IEC 61439-1 IEC 61439-2
Product certifications	ASEFA
Quantity per set	Set of 1
Height	400 mm
Width	500 mm
Net weight	1.62 kg
Material	Steel
Surface finish	Smooth Matt
Protective treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Colour	White (RAL 9001)

### Environment

IK degree of protection	IK07 conforming to EN/IEC 62262
-------------------------	---------------------------------

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Not applicable, out of EU RoHS legal scope
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations

## Contractual warranty

Warranty	18 months
----------	-----------