



Main

Range	Prisma
Range compatibility	Prisma G
Product or component type	Front plate
Accessory / separate part category	Installation accessory
Type of front plate	Cut-out
Installed device	Compact : fixed NSXm without earth leakage protection - control: direct rotary handle - horizontal installation
Poles description	1 x 3P or 4P : mounting plate support : NSXm horizontal installation
Operating position	Horizontal

Complementary

Enclosure/Cubicle description	Floor-standing enclosure - width 850 mm
Connection position	Direct connection
Number of vertical modules [50 mm]	3
Standards	IEC 61439-2 IEC 61439-1
Product certifications	ASEFA
Quantity per set	Set of 1
Height	150 mm
Surface finish	Matt Smooth
Protective treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Colour	White RAL 9001

Environment

IK degree of protection	IK07 conforming to EN/IEC 62262
-------------------------	---------------------------------