

Main

Range	Prisma
Range compatibility	Prisma P Prisma G
Product or component type	Front plate
Accessory / separate part category	Installation accessory
Type of front plate	Transparent
Installed device	TeSys : fixed GV3Pxx1 + LC1D40 to D65 - horizontal installation
Poles description	3 x 3P : modular rail support : GV3Pxx1 + LC1D40 to D65 horizontal installation

Complementary

Enclosure/Cubicle description	Floor-standing duct - width 300 mm Wall-mounted duct - width 300 mm Cubicle - width 400 mm, depth 400 mm
Number of vertical modules [50 mm]	6
Standards	IEC 61439-2 IEC 61439-1
Product certifications	ASEFA
Quantity per set	Set of 1
Height	300 mm
Width	300 mm
Product weight	0.76 kg
Material	Glass
Surface finish	Matt Smooth
Protective treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Colour	White RAL 9001


Environment

IK degree of protection	IK07 conforming to EN/IEC 62262
-------------------------	---------------------------------

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 0807 - Schneider Electric declaration of conformity
------------------------	---

 [Schneider Electric declaration of conformity](#)

Product environmental profile	Available
	 Product Environmental Profile

Product end of life instructions	Need no specific recycling operations
----------------------------------	---------------------------------------

Contractual warranty

Warranty period	18 months
-----------------	-----------
