



### Main

Range	Prisma
Range compatibility	Prisma P Prisma G
Product or component type	Front plate
Accessory / separate part category	Installation accessory
Type of front plate	Transparent
Installed device	Power meters : kilowatt-hour meters - vertical installation
Poles description	1 x 4P : mounting plate support : kilowatt-hour meters vertical installation

### Complementary

Enclosure/Cubicle description	Floor-standing duct - width 300 mm Wall-mounted duct - width 300 mm Cubicle - width 400 mm, depth 400 mm
Number of vertical modules [50 mm]	9
Standards	IEC 61439-2 IEC 61439-1
Product certifications	ASEFA
Quantity per set	Set of 1
Height	450 mm
Width	300 mm
Product weight	1.14 kg
Material	Glass
Surface finish	Matt Smooth
Protective treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Colour	White RAL 9001

### Environment


IK degree of protection	IK07 conforming to EN/IEC 62262
-------------------------	---------------------------------

### Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 0807 - Schneider Electric declaration of conformity
------------------------	-----------------------------------------------------------------------

 [Schneider Electric declaration of conformity](#)

---

Product environmental profile	Available
	 <a href="#">Product Environmental Profile</a>

---

Product end of life instructions	Need no specific recycling operations
----------------------------------	---------------------------------------

---

### Contractual warranty

---

Warranty period	18 months
-----------------	-----------

---