



### Main

Range	Prisma
Range compatibility	Prisma P
Product or component type	Mounting plate
Accessory / separate part category	Installation accessory
Installed device	<p>Compact : plug-in NSX100...160 with earth leakage protection - control: toggle - vertical installation</p> <p>Compact : plug-in NSX250 with earth leakage protection - control: toggle - vertical installation</p> <p>Compact : plug-in NSX100...160 without earth leakage protection - control: toggle - vertical installation</p> <p>Compact : plug-in NSX250 without earth leakage protection - control: toggle - vertical installation</p> <p>Compact : drawout NSX100...160 without earth leakage protection - control: toggle - vertical installation</p> <p>Compact : drawout NSX250 without earth leakage protection - control: toggle - vertical installation</p> <p>Compact : plug-in NSX100...160 without earth leakage protection - control: direct front rotary handle - vertical installation</p> <p>Compact : plug-in NSX250 without earth leakage protection - control: direct front rotary handle - vertical installation</p> <p>Compact : drawout NSX100...160 without earth leakage protection - control: direct front rotary handle - vertical installation</p> <p>Compact : drawout NSX250 without earth leakage protection - control: direct front rotary handle - vertical installation</p> <p>Compact : plug-in NSX100...160 without earth leakage protection - control: motor mechanism - vertical installation</p> <p>Compact : plug-in NSX250 without earth leakage protection - control: motor mechanism - vertical installation</p> <p>Compact : drawout NSX100...160 without earth leakage protection - control: motor mechanism - vertical installation</p> <p>Compact : drawout NSX250 without earth leakage protection - control: motor mechanism - vertical installation</p> <p>Compact : drawout NSX100...160 with earth leakage protection - control: toggle - vertical installation</p> <p>Compact : drawout NSX250 with earth leakage protection - control: toggle - vertical installation</p> <p>Compact : plug-in NSX100...160 with earth leakage protection - control: direct front rotary handle - vertical installation</p> <p>Compact : plug-in NSX250 with earth leakage protection - control: direct front rotary handle - vertical installation</p> <p>Compact : drawout NSX100...160 with earth leakage protection - control: direct front rotary handle - vertical installation</p> <p>Compact : drawout NSX250 with earth leakage protection - control: direct front rotary handle - vertical installation</p>

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Compact : plug-in NSX100...160 with earth leakage protection - control: motor mechanism - vertical installation  
 Compact : plug-in NSX250 with earth leakage protection - control: motor mechanism - vertical installation  
 Compact : drawout NSX100...160 with earth leakage protection - control: motor mechanism - vertical installation  
 Compact : drawout NSX250 with earth leakage protection - control: motor mechanism - vertical installation

Poles description	4 x 3P : plug-in : NSX100...160 vertical installation 4 x 3P : plug-in : NSX250 vertical installation 2 x 3P : drawout : NSX100...160 vertical installation 2 x 3P : drawout : NSX250 vertical installation 3 x 4P : plug-in : NSX100...160 vertical installation 3 x 4P : plug-in : NSX250 vertical installation 2 x 4P : drawout : NSX100...160 vertical installation 2 x 4P : drawout : NSX250 vertical installation
-------------------	--

## Complementary

Installation description	Cubicle - width 650 mm, depth 400 mm
Number of vertical modules [50 mm]	8 module(s) : NSX100...160 without earth leakage protection , direct in 650 mm Wide cubicle 9 module(s) : NSX250 without earth leakage protection , direct in 650 mm Wide cubicle 10 module(s) : NSX100...160 with earth leakage protection , direct in 650 mm Wide cubicle 11 module(s) : NSX250 with earth leakage protection , direct in 650 mm Wide cubicle 7 module(s) : NSX100...160 without earth leakage protection , Linergy FC in 650 mm Wide cubicle 9 module(s) : NSX100...160 without earth leakage protection , direct in 650 mm Wide cubicle 8 module(s) : NSX250 without earth leakage protection , Linergy FC in 650 mm Wide cubicle 10 module(s) : NSX250 without earth leakage protection , direct in 650 mm Wide cubicle 9 module(s) : NSX100...160 with earth leakage protection , Linergy FC in 650 mm Wide cubicle 11 module(s) : NSX100...160 with earth leakage protection , direct in 650 mm Wide cubicle 9 module(s) : NSX100...160 with earth leakage protection , direct in 650 mm Wide cubicle 10 module(s) : NSX250 with earth leakage protection , Linergy FC in 650 mm Wide cubicle 12 module(s) : NSX250 with earth leakage protection , direct in 650 mm Wide cubicle 10 module(s) : NSX250 with earth leakage protection , direct in 650 mm Wide cubicle
Height	200 mm
Product weight	3.2 kg
Surface finish	Smooth Matt
Protective treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Colour	White RAL 9001

## Environment

Standards	IEC 61439-2
Product certifications	ASEFA

## Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0807 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product environmental profile	Available <a href="#">Product Environmental Profile</a>
Product end of life instructions	Available <a href="#">End of Life Information</a>

## Contractual warranty

Warranty period	18 months
-----------------	-----------