



Main

Range	Prisma
Range compatibility	Prisma P
Product or component type	Mounting plate
Accessory / separate part category	Installation accessory
Installed device	<p>Easypact : fixed EZC400 - control: toggle - horizontal installation</p> <p>Easypact : fixed CVS400 without earth leakage protection - control: toggle - horizontal installation</p> <p>Easypact : fixed CVS630 without earth leakage protection - control: toggle - horizontal installation</p> <p>Compact : fixed NSX400 without earth leakage protection - control: toggle - horizontal installation</p> <p>Compact : fixed NSX630 without earth leakage protection - control: toggle - horizontal installation</p> <p>Compact : fixed NSX400 with earth leakage protection - control: toggle - horizontal installation</p> <p>Compact : fixed NSX630 with earth leakage protection - control: toggle - horizontal installation</p> <p>Easypact : fixed CVS400 with earth leakage protection - control: toggle - horizontal installation</p> <p>Easypact : fixed CVS630 with earth leakage protection - control: toggle - horizontal installation</p> <p>Easypact : fixed EZC630 - control: toggle - horizontal installation</p>
Poles description	<p>1 x 3P : fixed : NSX400 horizontal installation</p> <p>1 x 3P : fixed : NSX630 horizontal installation</p> <p>1 x 3P : fixed : EZC400 horizontal installation</p> <p>1 x 3P : fixed : EZC630 horizontal installation</p> <p>1 x 3P : fixed : CVS400 horizontal installation</p> <p>1 x 3P : fixed : CVS630 horizontal installation</p>

Complementary

Installation description	Cubicle - width 650 mm, depth 400 mm
Number of vertical modules [50 mm]	<p>4 module(s) : CVS400 without earth leakage protection , direct in 650 mm Wide cubicle</p> <p>4 module(s) : CVS630 without earth leakage protection , direct in 650 mm Wide cubicle</p> <p>4 module(s) : EZC400, direct in 650 mm Wide cubicle</p> <p>4 module(s) : EZC630, direct in 650 mm Wide cubicle</p> <p>4 module(s) : NSX400 without earth leakage protection , direct in 650 mm Wide cubicle</p> <p>4 module(s) : NSX630 without earth leakage protection , direct in 650 mm Wide cubicle</p> <p>4 module(s) : CVS400 with earth leakage protection , direct in 650 mm Wide cubicle</p> <p>4 module(s) : CVS630 with earth leakage protection , direct in 650 mm Wide cubicle</p> <p>4 module(s) : NSX400 with earth leakage protection , direct in 650 mm Wide cubicle</p> <p>4 module(s) : NSX630 with earth leakage protection , direct in 650 mm Wide cubicle</p>
Height	200 mm

Product weight	1.48 kg
Surface finish	Smooth Matt
Protective treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Colour	White RAL 9001

Environment

Standards	IEC 61439-2
Product certifications	ASEFA

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0722 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available Product Environmental Profile
Product end of life instructions	Available End of Life Information

Contractual warranty

Warranty period	18 months
-----------------	-----------