



Main

Range	Prisma
Product or component type	630/1600 A measurement CT casing
Accessory / separate part category	Busbar accessory
Range compatibility	Prisma P enclosure
Additional information	630/1600 A measurement CT casing The top and bottom plates have knock-outs for the passage of cables or bars Casing with lead-sealable panels at the front or the rear

Complementary

Enclosure/Cubicle description	Cubicle - width 650 mm
Product destination	For the device compartment of a 400 mm deep framework For the device compartment of a 600 mm deep cubicle
Kit composition	2 depth-adjustable uprights 2 longitudinal cross-members with holes
Number of vertical modules [50 mm]	12
Height	571 mm
Width	575 mm
Net weight	18.34 kg
Material	Steel
Surface finish	Matt Smooth
Protective treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder

Offer Sustainability

Sustainable offer status	Green Premium product
RECh Regulation	RECh Declaration
RECh free of SVHC	Yes
EU RoHS Directive	Not applicable, out of EU RoHS legal scope
Mercury free	Yes
RoHS exemption information	Yes

China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information

Contractual warranty

Warranty	18 months
----------	-----------
