



### Main

Range	Prisma
Range compatibility	Prisma P
Product or component type	Mounting plate
Accessory / separate part category	Installation accessory
Installed device	Fupact : fixed INF200...250 - control: extended rotary handle - vertical installation Fupact : fixed INF400 - control: extended rotary handle - vertical installation Fupact : fixed INF630...800 - control: extended rotary handle - vertical installation
Poles description	1 x 3P : fixed : INF200...250 vertical installation 1 x 3P : fixed : INF400 vertical installation 1 x 3P : fixed : INF630...800 vertical installation 1 x 4P : fixed : INF200...250 vertical installation 1 x 4P : fixed : INF400 vertical installation 1 x 4P : fixed : INF630...800 vertical installation

### Complementary

Installation description	Cubicle - width 650 mm, depth 400 mm
Number of vertical modules [50 mm]	11 module(s) : INF630...800, direct in 650 mm Wide cubicle 9 module(s) : INF200...250, direct in 650 mm Wide cubicle 9 module(s) : INF400, direct in 650 mm Wide cubicle
Height	300 mm
Product weight	3.62 kg
Surface finish	Matt Smooth
Protective treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Colour	White RAL 9001

### Environment

Standards	IEC 61439-2
Product certifications	ASEFA

## Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1018 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product environmental profile	Available <a href="#">Product Environmental Profile</a>
Product end of life instructions	Available <a href="#">End of Life Information</a>

## Contractual warranty

Warranty period	18 months
-----------------	-----------