



Main

Range	Prisma
Range compatibility	Prisma P
Product or component type	Mounting plate
Accessory / separate part category	Installation accessory
Installed device	Fupact : fixed INF32 - control: extended rotary handle - vertical installation Fupact : fixed INF32 - control: extended rotary handle - horizontal installation Fupact : fixed INF40 - control: extended rotary handle - vertical installation Fupact : fixed INF40 - control: extended rotary handle - horizontal installation
Poles description	1 x 3P : fixed : INF32 horizontal installation 1 x 4P : fixed : INF32 horizontal installation 1 x 3P : fixed : INF40 horizontal installation 1 x 4P : fixed : INF40 horizontal installation 4 x 3P : fixed : INF32 vertical installation 4 x 3P : fixed : INF40 vertical installation 3 x 4P : fixed : INF32 vertical installation 3 x 4P : fixed : INF40 vertical installation

Complementary

Installation description	Cubicle - width 650 mm, depth 400 mm
Number of vertical modules [50 mm]	3 module(s) : INF32, direct in 650 mm Wide cubicle 3 module(s) : INF40, direct in 650 mm Wide cubicle
Height	300 mm
Width	575 mm
Product weight	2.14 kg
Surface finish	Matt Smooth
Protective treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Colour	White RAL 9001

Environment

Standards	IEC 61439-2
-----------	-------------

Product certifications	ASEFA
------------------------	-------

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0807 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available Product Environmental Profile
Product end of life instructions	Available End of Life Information

Contractual warranty

Warranty period	18 months
-----------------	-----------
