



Main

Range	Prisma
Range compatibility	Prisma P
IP degree of protection	IP30
Product or component type	Front plate
Accessory / separate part category	Installation accessory
Type of front plate	Cut-out
Installed device	Easypact : fixed EZC400 - control: toggle - horizontal installation Easypact : fixed CVS400 without earth leakage protection - control: toggle - horizontal installation Easypact : fixed CVS630 without earth leakage protection - control: toggle - horizontal installation Easypact : fixed CVS400 with earth leakage protection - control: toggle - horizontal installation Easypact : fixed CVS630 with earth leakage protection - control: toggle - horizontal installation Easypact : fixed EZC630 - control: toggle - horizontal installation
Poles description	1 x 3P : mounting plate support : CVS400 horizontal installation 1 x 3P : mounting plate support : CVS630 horizontal installation 1 x 3P : mounting plate support : EZC400 horizontal installation 1 x 3P : mounting plate support : EZC630 horizontal installation
Operating position	Horizontal

Complementary

Enclosure/Cubicle description	Cubicle - width 650 mm, depth 400 mm
Connection position	Direct connection
Type of front plate	Cut-out
Number of vertical modules [50 mm]	4
Standards	IEC 61439-2 IEC 61439-1
Product certifications	ASEFA
Quantity per set	Set of 1
Height	200 mm
Width	500 mm
Product weight	0.8 kg

Material	Steel
Surface finish	Matt Smooth
Protective treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Colour	White RAL 9001

Environment

IK degree of protection	IK07 conforming to EN/IEC 62262
-------------------------	---------------------------------

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0701 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available Product Environmental Profile
Product end of life instructions	Available End of Life Information

Contractual warranty

Warranty period	18 months
-----------------	-----------