



Main

Range	Prisma
Range compatibility	Prisma P
Product or component type	Front plate
Accessory / separate part category	Installation accessory
Type of front plate	Cut-out
Installed device	Compact : fixed NS630b...1000 - control: motor mechanism - vertical installation Compact : fixed NS1250 - control: motor mechanism - vertical installation Compact : fixed NS1600 - control: motor mechanism - vertical installation
Poles description	1 x 3P : mounting plate support : NS630b...1000 vertical installation 1 x 3P : mounting plate support : NS1250 vertical installation 1 x 3P : mounting plate support : NS1600 vertical installation 1 x 4P : mounting plate support : NS630b...1000 vertical installation 1 x 4P : mounting plate support : NS1250 vertical installation 1 x 4P : mounting plate support : NS1600 vertical installation
Operating position	Vertical

Complementary

Enclosure/Cubicle description	Cubicle - width 650 mm, depth 400 mm Cubicle - width 650 mm, depth 800 mm
Connection position	Front connection Rear connection
Number of vertical modules [50 mm]	7
Standards	IEC 61439-2 IEC 61439-1
Product certifications	ASEFA
Quantity per set	Set of 1
Height	350 mm
Width	500 mm
Product weight	1.52 kg
Material	Steel

Surface finish	Matt Smooth
Protective treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Colour	White RAL 9001

Environment

IK degree of protection	IK07 conforming to EN/IEC 62262
-------------------------	---------------------------------

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0807 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available Product Environmental Profile
Product end of life instructions	Available End of Life Information

Contractual warranty

Warranty period	18 months
-----------------	-----------