



### Main

Range	Prisma
Range compatibility	Prisma P
Product or component type	Front plate
Accessory / separate part category	Installation accessory
Type of front plate	Cut-out
Installed device	Masterpact: drawout NW08...16 - control: toggle - vertical installation Masterpact: drawout NW20...25 - control: toggle - vertical installation Masterpact: drawout NW32 - control: toggle - vertical installation
Poles description	1 x 3P: mounting plate support: NW08...16 vertical installation 1 x 4P: mounting plate support: NW08...16 vertical installation 1 x 3P: mounting plate support: NW20...25 vertical installation 1 x 4P: mounting plate support: NW20...25 vertical installation 1 x 3P: mounting plate support: NW32 vertical installation 1 x 4P: mounting plate support: NW32 vertical installation
Operating position	Horizontal

### Complementary

Enclosure/Cubicle description	Cubicle - width 650 mm depth 600 mm Cubicle - width 650 mm depth 1000 mm
Connection position	Front connection Rear connection
Number of vertical modules [50 mm]	10
Standards	IEC 61439-2 IEC 61439-1
Product certifications	ASEFA
Quantity per set	Set of 1
Height	500 mm
Net weight	1.76 kg
Surface finish	Smooth Matt
Protective treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Colour	White (RAL 9001)

## Environment

IK degree of protection	IK07 conforming to EN/IEC 62262
-------------------------	---------------------------------

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Not applicable, out of EU RoHS legal scope
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End of Life Information</a>