



### Main

Range	Prisma
Range compatibility	Prisma P
IP degree of protection	IP20
Product or component type	Front plate
Accessory / separate part category	Installation accessory
Type of front plate	Cut-out
Installed device	Fupact : fixed ISFL160 - control: fuse carriers handle - vertical installation Fupact : fixed ISFL250...630 - control: fuse carriers handle - vertical installation
Poles description	10 x 3P : mounting plate support : ISFL160 vertical installation 5 x 3P : mounting plate support : ISFL250...630 vertical installation

### Complementary

Enclosure/Cubicle description	Cubicle - width 650 mm, depth 400 mm
Connection position	Rear connection
Number of vertical modules [50 mm]	24
Standards	IEC 61439-2 IEC 61439-1
Product certifications	ASEFA
Quantity per set	Set of 1
Width	570 mm
Product weight	10.06 kg
Material	Steel
Surface finish	Smooth Matt
Protective treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Colour	White RAL 9001

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

## Environment

---

IK degree of protection	IK07 conforming to EN/IEC 62262
-------------------------	---------------------------------

---

## Offer Sustainability

---

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1018 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product environmental profile	Available <a href="#">Product Environmental Profile</a>
Product end of life instructions	Available <a href="#">End of Life Information</a>

---

## Contractual warranty

---

Warranty period	18 months
-----------------	-----------

---