



Main

Range	Linery
Product name	Linery FM
IP degree of protection	IP20
Product or component type	Device feeder
Product compatibility	Spacial enclosures

Complementary

Mounting support	DIN rail Plain backplate Slotted backplate
Mounting mode	By screws Clip-on
Installed device	Modular device
Poles description	3P + N
[Ue] rated operational voltage	440 V AC
[Ui] rated insulation voltage	500 V AC 50/60 Hz
[Uimp] rated impulse withstand voltage	6 kV
[Ie] rated operational current	80 A
[Ipk] rated peak withstand current	12 kA
I ² t on activation	2400000 A ² .s
Connections - terminals	Supply : tunnel type terminal 25 mm ² (flexible) Supply : tunnel type terminal 35 mm ² (rigid) Distribution : quick-connect terminal strips (phase) , 18 x 4...6 mm ² Distribution : quick-connect terminal strips (neutral) , 18 x 4...6 mm ²
Total number of 18 mm modules	24
Product weight	0.902 kg
Colour	Anthracite grey RAL 7016

Environment

Standards	IEC 61439-1 inside Prisma IEC 61439-2 inside Prisma IEC 60947-7-1
Product certifications	ASEFA

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 1001 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold

Contractual warranty

Warranty period	18 months
-----------------	-----------
