



Main

Range	Lineryy
Product name	Lineryy FM
IP degree of protection	IPxx B
Product or component type	Device feeder
Product compatibility	Spacial enclosures

Complementary

Mounting support	DIN rail Plain backplate Slotted backplate
Installed device	Modular device
Poles description	3P
[Ue] rated operational voltage	690 V AC
[Ui] rated insulation voltage	750 V AC 50/60 Hz
[Uimp] rated impulse withstand voltage	8 kV
[Ie] rated operational current	200 A
[Ipk] rated peak withstand current	20 kA
I ² t on activation	6700000 A ² .s
Connections - terminals	Supply : crimped lug 50 mm ² Supply : flexible bars, 20 x 3 mm Distribution : quick-connect terminal strips (phase) , 12 x 4...10 mm ² (flexible) Distribution : quick-connect terminal strips (phase) , 12 x 4...10 mm ² (rigid) Distribution : quick-connect terminal strips (neutral) , 18 x 4...10 mm ² (flexible) Distribution : quick-connect terminal strips (neutral) , 18 x 4...10 mm ² (rigid)
Total number of 18 mm modules	24
Product weight	1.32 kg
Colour	Anthracite grey RAL 7016

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Environment

Standards	IEC 61439-1 inside Prisma IEC 61439-2 inside Prisma IEC 60947-7-1
Product certifications	ASEFA

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0823 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available Product Environmental Profile
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------