



Main

Range	Linery
Product name	Linery DX
IP degree of protection	IPxx B
Product or component type	Distribution block
Product compatibility	Spacial enclosures

Complementary

Location of connection	Bottom
Mounting support	DIN rail
Poles description	4P
[Ue] rated operational voltage	440 V AC
[Ui] rated insulation voltage	500 V AC
[Uimp] rated impulse withstand voltage	8 kV
[Ie] rated operational current	63 A at 40 °C
Connections - terminals	Supply : tunnel type terminal 16 mm ² (flexible) Supply : tunnel type terminal 25 mm ² (rigid) Distribution : spring terminal (phase) , 12 x 2.5...6 mm ² (flexible) Distribution : spring terminal (phase) , 12 x 2.5...6 mm ² (rigid) Distribution : spring terminal (neutral) , 12 x 2.5...6 mm ² (flexible) Distribution : spring terminal (neutral) , 12 x 2.5...6 mm ² (rigid)
Total number of 18 mm modules	4
Product weight	0.29 kg

Environment

Pollution degree	3
Resistance to incandescent wire	960 °C conforming to IEC 60695-2-11
Standards	IEC 61439-2 IEC 60947-7-1 IEC 61439-1
Product certifications	ASEFA

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 1001 - Schneider Electric declaration of conformity
------------------------	---

Contractual warranty

Warranty period	18 months
-----------------	-----------
