



Main

Range	Lineryy
Product name	Lineryy BS
IP degree of protection	IPxx B
Product or component type	Distribution block
Product compatibility	Spacial enclosures

Complementary

Mounting support	Plain backplate Prisma upright
Mounting mode	Horizontal Vertical
Poles description	4P
[Ue] rated operational voltage	440 V AC
[Ui] rated insulation voltage	750 V AC
[Uimp] rated impulse withstand voltage	8 kV
[Ie] rated operational current	160 A
[Icw] rated short-time withstand current	10 kA 1 s
[Ipk] rated peak withstand current	30 kA
I ² t on activation	100000000 A ² .s
Busbar cross section	15 x 5 mm
Connections - terminals	Supply : crimped lug 50 mm ² Supply : flexible bars, 20 x 2 mm Distribution : M6 holes (phase) , 13 x 1...50 mm ²
Height	235 mm
Width	470 mm
Depth	115 mm
Product weight	2.72 kg

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Environment

Standards	IEC 61439-2 EN/IEC 61439-1
Product certifications	ASEFA

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0819 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available Product Environmental Profile
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------