



### Main

Range	Linery
Product name	Linery BW
IP degree of protection	IPxx B
Product or component type	Universal power supply block
Accessory / separate part category	Current distribution accessory
Provided equipment	Without cable

### Complementary

Cubicle-device connection	Linery BW busbar
Poles description	4P
Installation description	<p>Cubicle - width 650 mm</p> <p>Floor-standing enclosure - width 600 mm</p> <p>Wall-mounted enclosure - width 600 mm</p> <p>Floor-standing duct - width 300 mm</p> <p>Wall-mounted duct - width 300 mm</p> <p>Floor-standing enclosure - width 850 mm</p> <p>Floor-standing enclosure + duct - width 600 + 300 mm</p> <p>Wall-mounted enclosure + duct - width 600 + 300 mm</p>
Installed device	<p>Compact : fixed INS250 - control: direct front rotary handle vertical installation</p> <p>Compact : fixed INV250 - control: direct front rotary handle vertical installation</p> <p>Fupact : fixed ISFT160 - control: fuse carriers handle vertical installation</p> <p>Easypact : fixed CVS100...160 without earth leakage protection - control: direct front rotary handle horizontal installation</p> <p>Easypact : fixed CVS250 without earth leakage protection - control: direct front rotary handle horizontal installation</p> <p>Easypact : fixed CVS100...160 without earth leakage protection - control: direct front rotary handle vertical installation</p> <p>Easypact : fixed CVS250 without earth leakage protection - control: direct front rotary handle vertical installation</p> <p>Easypact : fixed CVS100...160 without earth leakage protection - control: toggle vertical installation</p> <p>Easypact : fixed CVS250 without earth leakage protection - control: toggle vertical installation</p> <p>Compact : fixed INV100 - control: direct front rotary handle vertical installation</p> <p>Fupact : fixed ISFT100N - control: fuse carriers handle vertical installation</p> <p>Compact : fixed NSX100...160 without earth leakage protection - control: toggle vertical installation</p> <p>Compact : fixed NSX250 without earth leakage protection - control: toggle vertical installation</p>

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Compact : fixed NSX100...160 without earth leakage protection - control: direct front rotary handle vertical installation  
 Compact : fixed NSX250 without earth leakage protection - control: direct front rotary handle vertical installation  
 Easycompact : fixed CVS100...160 with earth leakage protection - control: direct front rotary handle horizontal installation  
 Easycompact : fixed CVS250 with earth leakage protection - control: direct front rotary handle horizontal installation  
 Easycompact : fixed CVS100...160 with earth leakage protection - control: direct front rotary handle vertical installation  
 Easycompact : fixed CVS250 with earth leakage protection - control: direct front rotary handle vertical installation  
 Easycompact : fixed CVS100...160 with earth leakage protection - control: toggle vertical installation  
 Easycompact : fixed CVS250 with earth leakage protection - control: toggle vertical installation  
 Compact : fixed NSX100...160 with earth leakage protection - control: toggle vertical installation  
 Compact : fixed NSX250 with earth leakage protection - control: toggle vertical installation  
 Compact : fixed NSX100...160 with earth leakage protection - control: direct front rotary handle vertical installation  
 Compact : fixed NSX250 with earth leakage protection - control: direct front rotary handle vertical installation  
 Compact : fixed INV200 - control: direct front rotary handle vertical installation  
 Fupact : fixed INF100...160 - control: extended rotary handle horizontal installation  
 Fupact : fixed ISFT160 - control: fuse carriers handle horizontal installation  
 Fupact : fixed ISFT250 - control: fuse carriers handle horizontal installation  
 Fupact : fixed ISFT250 - control: fuse carriers handle vertical installation  
 Compact : fixed INV160 - control: direct front rotary handle vertical installation

[I <sub>e</sub> ] rated operational current	250 A
Quantity per set	Set of 1
Product weight	0.44 kg

## Environment

Standards	IEC 61439-1, inside Prisma IEC 61439-2, inside Prisma
Product certifications	ASEFA

## Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0850 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product environmental profile	Available <a href="#">Product Environmental Profile</a>
Product end of life instructions	Need no specific recycling operations

## Contractual warranty

Warranty period	18 months
-----------------	-----------