



Main

| | |
|------------------------------------|--------------------------------|
| Range | Prisma |
| Product or component type | Connection |
| Accessory / separate part category | Current distribution accessory |

Complementary

| | |
|---|--|
| Cubicle-device connection | Linergy BS busbar |
| Installation description | Floor-standing duct - width 300 mm Wall-mounted duct - width 300 mm |
| Installed device | Compact : fixed NSX400 without earth leakage protection - control: toggle vertical installation Compact : fixed NSX400 without earth leakage protection - control: direct front rotary handle vertical installation Compact : fixed NSX400 with earth leakage protection - control: toggle vertical installation Easypact : fixed CVS400 without earth leakage protection - control: toggle vertical installation Easypact : fixed CVS630 without earth leakage protection - control: toggle vertical installation Easypact : fixed CVS400 without earth leakage protection - control: direct front rotary handle vertical installation Easypact : fixed CVS630 without earth leakage protection - control: direct front rotary handle vertical installation Easypact : fixed CVS400 with earth leakage protection - control: toggle vertical installation Easypact : fixed CVS630 with earth leakage protection - control: toggle vertical installation Compact : fixed NSX630 without earth leakage protection - control: toggle vertical installation Compact : fixed NSX630 without earth leakage protection - control: direct front rotary handle vertical installation Compact : fixed NSX630 with earth leakage protection - control: toggle vertical installation Compact : fixed INS320...400 - control: direct front rotary handle vertical installation Compact : fixed INS500...630 - control: direct front rotary handle vertical installation Compact : fixed INV320...400 - control: direct front rotary handle vertical installation Compact : fixed INV500...630 - control: direct front rotary handle vertical installation |
| [I _e] rated operational current | 630 A |
| Quantity per set | Set of 1 |
| Product weight | 2.28 kg |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications.

Environment

| | |
|------------------------|----------------------------|
| Standards | IEC 61439-2 IEC 61439-1 |
| Product certifications | ASEFA |

Offer Sustainability

| | |
|----------------------------------|---|
| Sustainable offer status | Green Premium product |
| RoHS (date code: YYWW) | Compliant - since 0812 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity |
| REACH | Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold |
| Product environmental profile | Available Product Environmental Profile |
| Product end of life instructions | Need no specific recycling operations |

Contractual warranty

| | |
|-----------------|-----------|
| Warranty period | 18 months |
|-----------------|-----------|