



Main

Range	Lineryy
Product name	Lineryy BW
IP degree of protection	IPxx B
Product or component type	Busbar
Busbar description	Insulated bar
Provided equipment	Clip-on covers
Quantity per set	Set of 1

Complementary

Poles description	3P
Installation direction	Vertical, operating position: rear
Installation description	Cubicle - width 650 mm Floor-standing enclosure - width 600 mm Wall-mounted enclosure - width 600 mm Floor-standing duct - width 300 mm Wall-mounted duct - width 300 mm Pack enclosure
[Ui] rated insulation voltage	500 V
[Uimp] rated impulse withstand voltage	8 kV
[Ie] rated operational current	125 A
[Icw] rated short-time withstand current	8.5 kA (1 s)
[Ipk] rated peak withstand current	20 kA
I ² t on activation	72250 kA ² .s
Permissible current	125 A
Length	450 mm
Product weight	1.2 kg
Type of busbar connection	M6 threaded hole
Connection pitch	Connection each 25 mm

Environment

Standards	IEC 61439-2 IEC 61439-1
Product certifications	ASEFA

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0834 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available Product Environmental Profile
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------