



### Main

Range	Lineryg
Product name	Lineryg BW
IP degree of protection	IPxx B
Product or component type	Busbar
Busbar description	Insulated bar
Quantity per set	Set of 1

### Complementary

Poles description	3P
Installation direction	Vertical, operating position: rear
Installation description	Cubicle - width 650 mm Floor-standing enclosure - width 600 mm Wall-mounted enclosure - width 600 mm
[Ui] rated insulation voltage	750 V
[Uimp] rated impulse withstand voltage	8 kV
[Ie] rated operational current	250 A
[Icw] rated short-time withstand current	13 kA (1 s)
[Ipk] rated peak withstand current	30 kA
I <sup>2</sup> t on activation	169000 kA <sup>2</sup> .s
Permissible current	250 A
Length	1000 mm
Product weight	3.86 kg
Type of busbar connection	M6 threaded hole
Connection pitch	Connection each 25 mm

### Environment

Standards	IEC 61439-2 IEC 61439-1
-----------	----------------------------

Product certifications	ASEFA
Mechanical robustness	Seismic tests : 2.5G with structure reinforcement conforming to IEC 60068-2-57

### Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0807 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product environmental profile	Available <a href="#">Product Environmental Profile</a>
Product end of life instructions	Need no specific recycling operations

### Contractual warranty

Warranty period	18 months
-----------------	-----------