



Main

Range	Lineryg
Product name	Lineryg BW
IP degree of protection	IPxx B
Product or component type	Busbar
Busbar description	Insulated bar
Quantity per set	Set of 1

Complementary

Poles description	4P
Installation direction	Vertical, operating position: rear
Installation description	Cubicle - width 650 mm Floor-standing enclosure - width 600 mm Wall-mounted enclosure - width 600 mm
[Ui] rated insulation voltage	750 V
[Uimp] rated impulse withstand voltage	8 kV
[Ie] rated operational current	400 A
[Icw] rated short-time withstand current	20 kA (1 s)
[Ipk] rated peak withstand current	52.5 kA
I ² t on activation	400000 kA ² .s
Permissible current	400 A
Length	1400 mm
Product weight	8.94 kg
Type of busbar connection	M6 threaded hole
Connection pitch	Connection each 25 mm

Environment

Standards	IEC 61439-2 IEC 61439-1
-----------	----------------------------

Product certifications	ASEFA
Mechanical robustness	Seismic tests : 2.5G with structure reinforcement conforming to IEC 60068-2-57

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0807 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available Product environmental
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------