



### Main

Range	Linergy
Product name	Linergy BW
IP degree of protection	IPxx B
Product or component type	One-piece connection
Provided equipment	With connection

### Complementary

Cubicle-device connection	Linergy BW busbar
Poles description	4P
Installation description	Cubicle - width 650 mm Floor-standing enclosure - width 600 mm Wall-mounted enclosure - width 600 mm Floor-standing duct - width 300 mm Wall-mounted duct - width 300 mm Pack enclosure - width 550 mm
Installed device	Multi 9 : NG125 Compact : NG160 Multi 9 : C120 Acti 9 : iC120 Compact : INS160
[Ie] rated operational current	160 A
Quantity per set	Set of 1
Length	165 mm
Product weight	0.48 kg

### Environment

Standards	IEC 61439-1, inside Prisma IEC 61439-2, inside Prisma
Product certifications	ASEFA

### Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 0841 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
Product environmental profile	Available

 Product Environmental Profile

---

Product end of life instructions	Need no specific recycling operations
----------------------------------	---------------------------------------

---

Contractual warranty

---

Warranty period	18 months
-----------------	-----------

---