



Main

Range	Linergy
Product name	Linergy BS
Product or component type	Copper busbar
Busbar description	Flat bar
Quantity per set	Set of 4

Complementary

Installation direction	Vertical, operating position: rear
Installation description	Cubicle - width 650 mm Floor-standing enclosure - width 600 mm Wall-mounted enclosure - width 600 mm Floor-standing duct - width 300 mm Wall-mounted duct - width 300 mm
[Ui] rated insulation voltage	1000 V
[Ie] rated operational current	250 A
[Ipk] rated peak withstand current	40 kA
I ² t on activation	169000 kA ² .s
Busbar cross section	20 x 5 mm
Length	1400 mm
Product weight	4.94 kg
Type of busbar connection	M6 threaded hole
Connection pitch	Connection each 25 mm
Support thickness	5 mm

Environment

Standards	IEC 61439-2 IEC 61439-1
Product certifications	ASEFA

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0807 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available Product Environmental Profile
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------