



Main

Range of products	Linery
Product name	Linery TA
Product or component type	Terminal block
Accessory / separate part category	Connection accessory
Product compatibility	Auxiliary connection

Complementary

Enclosure/Cubicle description	Cubicle Floor-standing enclosure Wall-mounted enclosure
[Ie] rated operational current	12 A 250 V AC IEC 40 °C 20 A 300 V AC UL 40 °C
Tightening torque	0.5...0.6 N.m
Connections - terminals	Input : screw terminal 10 pin(s) - cable cross section: 0.2...4 mm ² - cable stiffness: rigid - without cable end Output : removable screw terminal block 20 pin(s) - cable cross section: 0.2...4 mm ² - cable stiffness: flexible - with cable end
Conductor material	Copper
Quantity per set	Set of 1
Height	50 mm
Width	65 mm
Depth	50 mm
Product weight	0.12 kg
Colour	Light grey RAL 7035

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 0707 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
Product environmental profile	Available Product Environmental Profile
Product end of life instructions	Available End of Life Information

Contractual warranty

Warranty period	18 months
-----------------	-----------
