



Main

Range	Linery
Product name	Linery BS
Product or component type	Copper busbar
Busbar description	Flat bar
Quantity per set	Set of 1

Complementary

Installation direction	Vertical, operating position: rear Vertical, operating position: lateral
Installation description	Cubicle - width 650 mm Cubicle - width 650 + 150 mm
[Ie] rated operational current	1000 A at 35 °C
[Icw] rated short-time withstand current	50 kA (1 s) for 7 supports (rear position) 15 kA (1 s) for 3 supports (lateral position) 30 kA (1 s) for 5 supports (lateral position) 15 kA (1 s) for 3 supports (rear position) 30 kA (1 s) for 5 supports (rear position) 50 kA (1 s) for 7 supports (lateral position)
Permissible current	1000 A at 35 °C: ≤ IP31 900 A at 35 °C: > IP31
Busbar cross section	80 x 5 mm
Length	1675 mm
Height	1830 mm
Width	150 mm
Depth	20 mm
Net weight	5.96 kg
Type of busbar connection	Ø 10 mm drilled hole
Connection pitch	Connection each 25 mm
Support thickness	5 mm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Environment

Standards	IEC 61439-1 IEC 61439-2
Product certifications	ASEFA

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Under investigation
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations End of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	18 months
----------	-----------