



### Main

Range	Linery
Product name	Linery BS
Product or component type	Copper busbar
Busbar description	Flat bar
Quantity per set	Set of 1

### Complementary

Installation direction	Horizontal, operating position: top Horizontal, operating position: bottom
Installation description	Cubicle - width 650 mm Cubicle - width 650 + 150 mm Cubicle duct - width 300 mm Cubicle duct - width 400 mm
[I <sub>e</sub> ] rated operational current	1400 A at 35 °C
[I <sub>lcw</sub> ] rated short-time withstand current	40 kA (1 s) for 2 supports 65 kA (1 s) for 3 supports 75 kA (1 s) for 4 supports
Permissible current	1400 A at 35 °C: ≤ IP31 1250 A at 35 °C: > IP31
Busbar cross section	60 x 10 mm
Length	2000 mm
Height	150 mm
Net weight	11.2 kg
Type of busbar connection	Without hole
Support thickness	10 mm

### Environment

Standards	IEC 61439-2 IEC 61439-1
-----------	----------------------------

Product certifications	ASEFA
------------------------	-------

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Under investigation
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations <a href="#">End of Life Information</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

### Contractual warranty

Warranty	18 months
----------	-----------